

Quantitative analysis of 3D structures in metal-oxide composites

Yu Wen^{1,2}, Ayako Hashimoto^{1,2,3}, Akihiko Hirata⁴, Hideki Abe^{1,5,6}

¹National Institute for Materials Science, 1-2-1 Sengen, Tsukuba, Ibaraki 305-0047, Japan

²Graduate School of Pure and Applied Sciences, University of Tsukuba, 1-1-1 Tennodai, Tsukuba, Ibaraki 305-8577, Japan

³PRESTO, JST, 4-1-8 Honcho, Kawaguchi, Saitama 332-0012, Japan

⁴Department of Materials Science, Waseda University, 3-4-1 Ohkubo, Shinjuku, Tokyo 169-8555, Japan

⁵Graduate School of Science and Technology, Saitama University, 255 Shimookubo, Saitama 338-8570, Japan

⁶CREST, JST, 4-1-8 Honcho, Kawaguchi, Saitama 332-0012, Japan

*Corresponding author: Yu.WEN@nims.go.jp

Homology analysis is an efficient topological method of interpreting the shape of data [1]. Several researches have applied it to describe and classify material structures, including metallic glasses [2] and polycrystals [3]. A quantitative interpretation of structures is necessary to find correlation in the structure-property relationship, which can be accomplished using the Betti numbers, β_i [4]. In the case of a two-dimensional (2D) structure image, the essential structure information, such as connectivity components and 1D holes, can be extracted and represented by β_0 and β_1 , respectively. Via STEM images, we previously showed that the connectivity of the CeO₂ phase, β_0 , plays an important role in the oxygen ionic transportation of Pt#CeO₂ composites [5]. However, this dependence does not work for the network structure, because isolated CeO₂ phases might be connected three-dimensionally. Therefore, 3D structural analysis is necessary for network structures to verify the relationship between the CeO₂ connectivity and ionic conductivity.

In the present study, Pt#CeO₂ composites with different structures were prepared by increasing the annealing temperature from 500 °C to 800 °C under CO and O₂ syngas. The ionic conductivities of the composites were measured using impedance spectroscopy, in the same manner as described in our previous work [5]. Focused ion beam (FIB) was used to thin the powders for observation. The STEM tomography technique was performed with a JEM-2100F (JEOL) microscope operated at 200 kV using a high tilt specimen holder. A tilt-series was acquired over an angular range of $\pm 60^\circ$ with a 2° tilt increment. Regarding the algorithm for 3D reconstruction, the weighted backprojection and simultaneous iterative reconstruction techniques were employed in DigitalMicrograph (Gatan). The generated stack slices were then binarized using the OpenCV library in Pycharm. Postprocessing including median filter, segmentation, and visualization was performed using the Avizo software (Thermo Fisher Scientific). The connectivity of the CeO₂ phases, i.e., the number of CeO₂ components (β_0), was obtained both through the Avizo analysis and chomp calculation [6].

For temperature increments in the range of 500–700 °C, the Pt#CeO₂ composites were exhibited a lamellar structure with increasing periodicity, whereas the composites annealed at 800 °C exhibited a network-like appearance. Ionic conductivity measurements indicated that the parameters, activation energy E , and pre-exponential factor σ_0 increased as the annealing temperature increased. This suggests that the CeO₂ connectivity was improved, and thus, β_0 decreased, from conclusions referred before. Figure 1 shows cross-sectional HAADF-STEM images and corresponding binary images of the Pt#CeO₂ composites annealed at 600 °C and 800 °C. The black and white phases correspond to the CeO₂ and Pt phases, respectively. Upon calculating the β_0 value from these 2D sectional binary images, the composites at 800 °C were found to exhibit the highest β_0 value, which is in contrast with the trends predicted via the ionic conductivity measurements. This is because, at 800 °C, some separated CeO₂ phases are

connected at a deeper thickness, as can be confirmed by the 3D structure of the 800 °C sample shown in Figure 2. The adjacent phases with the same color belong to the same component. From the 3D structure analysis, the β_0 value of the 800 °C sample was found to be lower than that of the 600 °C sample, which is inversely proportional to the ionic conductivity parameters (E and σ_0). Further 3D reconstructions of the 500 °C and 700 °C samples will be performed in the future. These results provide a strong evidence for the relationship between the CeO₂ phase connectivity and ionic conductivity of Pt#CeO₂ composites.




Figure 1. STEM images and corresponding binary images of Pt#CeO₂ prepared at 600deg (a)-(b) and 800deg (c)-(d).




Figure 2. Reconstructed 3D image of Pt#CeO₂ composites annealed at 800°C.

References

- [1] T. Kaczynski et al., Springer Science & Business Media, 157 (2006).
- [2] A Hirata et al., Structural analysis of metallic glasses with computational homology, Springer Japan (2016).
- [3] T. Wanner et al., Acta Mater., 58 102 (2010).
- [4] H. Poincaré. Analysis situs, Journal de l'École Polytechnique Serie 2, 1 (1895)
- [5] Y. Wen et al., Appl. Phys. Lett., 118 054102 (2021).
- [6] W Kalies, et al., Computational homology program, Available from: <http://www.math.gatech.edu/~chom/> (2003).